



Dear customer,

Please fill out this order form completely for your UE custom in-ear monitors. On the second page you will find the instructions for the audiologist. Please print this sheet and take it with you to your ear impression appointment and submit it there. Then please send the completed form together with your ear impressions to Fischer Amps.

We will send you an order confirmation by email within 5 days of receipt.

• model selection (pier	ase mark the desir	ed model):
UE PREMIER (21 drivers, 5-way crossover)		Ambient option
UE LIVE (8 drivers, 5-way crossover)		Ambient option
UE 18+ PRO (6 drivers, 4-way crossover)		Ambient option
UE 11 PRO (4 drivers, 3-way crossover)		Ambient option
UE 7 PRO (3 drivers, 3-way crossover)		Ambient option
UE 6 PRO (3 drivers, 3-way crossover)		Ambient option
UE 5 PRO (2 drivers, 2-way crossover)		Ambient option
UE RR + PRO (3 drive	ers, 3-way crossover)	Ambient option
• Color and design selection	on, page 3 (desired co	blor / design)*:
• Further design options:	without UE Logo	(surcharge) 🔲 own logo oder graphic (surcharge)
• Cable length:	🗌 50ʻ (127 cm)	🗌 64' (164 cm)
• Cable color:	🗌 clear	🗌 black
• Transport case:	square	
Name on Case (If different f	rom First Name and Name):	(Max.25 letters)
		(Max. 25 letters)
Further informations :		
 Further informations : Name*: 		
 Further informations : Name*: Street: 		-irst Name*:
 Further informations : Name*: Street: Zip Code: 	Town:	-irst Name*:
 Further informations : Name*: Street: Zip Code: Mobile phone: 	Town:	-irst Name*: Country:
Further informations : Name*: Street: Zip Code: Mobile phone: Notes: With my signature, I place	Town:	-irst Name*: Country: Email:
Further informations :	Town: The binding order a re the binding order a	First Name*:Country:Country:Country:Country:

FISCHER AMPS, Hans-Ulrich-Breymann-Str. 3, 74706 Osterburken / Germany Email: info@fischer-amps.de, Phone: +49 6291 64879 0



Important information on taking ear impressions for professional custom-made in-ear earphones:

- 1. For taking ear impressions, use fine-grain, easily flowable ear impression silicone for a high level of impression precision and, if possible, flat impression pads or cotton pads that match the diameter of the ear canal.
- 2. When taking the ear impression, the mouth should be relaxed and closed until the ear impressions are taken. No chewing movements during the curing process, please!
- 3. When inserting the ear impression material into the ear, ensure that all areas of the outer ear shown in the example image and up to the second bend of the ear canal (see below) are completely molded without air traps. It is also important that ear impression material is built up in the area of the base, since the area of the outer concha is also very important for the construction of the earpiece and the positioning of the connector.
- 4. If the finished ear impressions are scanned with an ear impression scanner, please save the scan data for transmission as Name_First name.stl files and send them as a file attachment by email to info@fischer-amps.de.

If you have further questions, please contact FISCHER AMPS: Phone: +49 6291 64879-0, Email: info@fischer-amps.de



FISCHER AMPS, Hans-Ulrich-Breymann-Str. 3, 74706 Osterburken / Germany Phone: +49 6291 -64879-0, Email: info@fischer-amps.de, www.fischer-amps.de

ULTIMATE EARS

HALO CHROME

LILAC

VIOLET

LUCKY RED

JET BLACK

UE COLORS / DESIGNS 2025

TRANSLUCENT **NO SURCHARGE** PROFESSIONAL **UE LOGO** UE UE UE NO SURCHARGE 18 UE CLEAR BRIGHT YELLOW GOLDEN YELLOW CITRUS ORANGE TRANSLUCENT TRANSLUCENT TRANSLUCENT UE UE UE 10 UE NEW LOGO SKY BLUE MARINE TEAL EMERALD GREEN **BUBBLE GUM PINK** TRANSLUCENT TRANSLUCENT TRANSLUCENT TRANSLUCENT **OWN INITIALS** SURCHARGE +50 € net UE UE UE (MAX.TWO LETTERS) LUCKY RED VIOLET JET BLACK TRANSLUCENT TRANSLUCENT TRANSLUCENT **NO SURCHARGE** SOLID OWN INITIALS CHROME UE 9 HALO SURCHARGE +200 € net SNOW WHITE **BRIGHT YELLOW** GOLDEN YELLOW CITRUS ORANGE UE UE UE HALO GOLD SKY BLUE MARINE TEAL **BUBBLE GUM PINK** EMERALD GREEN UE UE UE UE





PROFESSIONAL



Dimensions : 8.3 x 7.3 x 4.1 cm

CABLES



The new UE SuperBax cable and IPX connection system.

No phase connector issues. Strong connection with double spring mechanism. sweat-proof, weather-proof, tour-proof.

Maximum strong, but also fine cable quality with low impedance. New fixable neck slider.

Available in 127 cm (50') and 163 cm (64') Color: transparent and black